





规格 01000062.J

文件号 A-2024-01000062.J

版本1

Shape and Size (mm)



Mounting Holes

Electrical Performance

Model	For Fuse	Rated Ampere	Rated Voltage	Contact Resistance	Insulation Resistance	Di-electronic Strength
01000062.J	ATU blade fuse	20A	250V	< 50MΩ	> 100MΩ @500V DC	> 2000V AC

Package

Model	Material	Qty
01000062.J	Brass or phosphor Bronze Finish: Tin-plated or Nickel-Plated	1000Pcs/Bag