

NOTES

MATERIAL

- 1.HOUSING MATERIAL: GLASS FILLED POLYESTER UL94V-0.
2.CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3.PLATING: GOLD PLATING OVER NICKEL.

ELECTRICAL





- 1.VOLTAGE RATING: 125 VAC RMS.
2.CURRENT RATING: 1.5 AMP.
3.CONTACT RESISTANCE: 40 MILLIOHMS MAX.
4.INSULATION RESISTANCE: 500 MEGOHMS MIN @ 100V DC .
5.DIELECTRIC DIELECTRIC
RESISTANCE: 500V DC RMS 50Hz. 1MIN.

MECHANICAL


- 1.DURRABILITY: 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG.F MAX.

ENVIRONMENTAL:

1. OPERATION: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. STORAGE: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$.



8	—
7	—
6	RX—
5	—
4	—
3	RX+
2	TX—
1	TX+
PIN	说明



PCBLAYOUT

TOL:±0.05

DIMENSION IN mm		厦门市辛译精密电子有限公司					
TOLERANCE UNLESS OTHERWISE SPECIFIED		Xiamen XinYi Xyeconn Electronics Co.,Ltd					
.X±0.35	X*± 3°	APR.	Alex	TITLE: RJ45 1x1 B 2 DIP			
.XX±0.25	.X*± 2°	CHK.	Jack	DWG NO. XY-RJ45R0-8PA-206			
.XXX±0.15	.XX*± 1°	DRA.	Can	PROJ. 		CUSTOMER DRAWING	
				SIZE A4	SCALE 1:1	SHEET 1/1	REV. A