



直边无脚



RBCOMMENDBD P.C.B PATTBRN LAY
OUT

规格 Specifications:

电性能 Electrical:

- 1.额定电流: Current Rating 1.5A/contact terminal
- 2.额定电压: Voltage Rating 30V DC
- 3.接触电阻: Contact Resistance 30 milliohms MAX
- 4.介电强度: Dielectric Withstanding Voltage: 500 V AC AT Sea Level
- 5.绝缘电阻: Insulation Resistance: 1000MEGA ohms MIN

机械性能 Mechanical:

- 1.插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf(MAX)
Unmate force: 1.02kgf(MIN)
- 2.端子保持力: Terminal Retention 1.2kgf(MIN)

材料 Material:

- 1.外壳: Housing: High Temperature Thermoplastics, PBT White/Black
- 2.端子: Contact: Copper Alloy C2680
- 3.壳: Shell: Copper Alloy C2680/SPCC

表面处理:

- 1.端子: Contact: Plated Gold in Mating Area
Tin On Solder Tails
- 2.壳: Shell: Nickel Plating

东莞市文章济美电子有限公司

UNLESS OTHERWISE SPECIFIED TOLERANCE		RBCOMMENDBD P.C.B PATTBRN LAY OUT		DRAWN	
.X	±0.20	H.Q.huocuy		UNIT	
.XX	±0.15	APPROVED		MM	
.XXX	±0.10	DATE		SCALE	
ANG.	±2°	2011.03.18		3/1	
				SIZE	
				A4	
				TITLE	
				USB-2.0AFSCZC14.2-B	
				PART NO.	
				DOC. NO.	
				REV.	
				A	