





直脚直边



1. Material:

Contaeis: Phosphone
Bronze
insulator: PBT+30%
G. F. UL 94V-0
Shell: SPCC

2. Mechanical:

Mating: 35N max.
Withdraw Force: 10N min.
Durability: 1500 cycles min.

3. Electrical:

Current-max (amps) 1.5A
Voltage-max (volts) 30V
Withstanding Voltage 750V AC
Contact Resistance (ohms) 30
milliohms max insulation
Resistance (ohms) 1000 Megohms
min.

4. Plating:

Contacts: Gold And Tin Over
Nickel Plated
Shell: Nickel over all plating.

5. Environmental:

temperature Range: -55 to 85

产品图
DRAWING

公差一览表
TOLERANCE TABLE

单位 UNIT	MM		INCH
.X	±0.20	.X	±
.XX	±0.10	.XX	±
.XXX	±0.05	.XXX	±

2013.08.29

东莞市文章济美电子有限公司

产品名称	USB-2.0AFSCZC17.0-B				
角法	制图	审核	核准		
比例	设计	核准	核准		
版本	图号	CKC1	张数	1/1	