




序号	品名	材质
①	0.8-C型WTB 刺破型公头端子	PA66 UL94 V-0 白色
②	0.8-C型WTB 刺破型公头端子	铜合金/镀金




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$ (含通电时的温度上升值)。
3. 额定电压: 30V, AC/DC。
4. 接触电阻: 初期 $\leq 0.02\Omega$, 环境试验后 $\leq 0.04\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ min。
6. 额定电流: 0.5A, AC/DC
(使用AWG#32, $0.038\pm 0.002\text{mm}$)。
7. 耐电压: AC 200V/1分钟。



Part No	CKT	A	B	C	D
XY-0.8-2A41-G	2	0.80	1.78	2.18	2.40
XY-0.8-3A41-G	3	1.60	2.58	2.98	3.20
XY-0.8-4A41-G	4	2.40	3.38	3.78	4.00
XY-0.8-5A41-G	5	3.20	4.18	4.58	4.80
XY-0.8-6A41-G	6	4.00	4.98	5.38	5.60
XY-0.8-7A41-G	7	4.80	5.78	6.18	6.40
XY-0.8-8A41-G	8	5.60	6.58	6.98	7.20
XY-0.8-9A41-G	9	6.40	7.38	7.78	8.00
XY-0.8-10A41-G	10	7.20	8.18	8.58	8.80
XY-0.8-11A41-G	11	8.00	8.98	9.38	9.60
XY-0.8-12A41-G	12	8.80	9.78	10.18	10.40
XY-0.8-13A41-G	13	9.60	10.58	10.98	11.20
XY-0.8-14A41-G	14	10.40	11.38	11.78	12.00
XY-0.8-15A41-G	15	11.20	12.18	12.58	12.80
XY-0.8-16A41-G	16	12.00	12.98	13.38	13.60
XY-0.8-17A41-G	17	12.80	13.78	14.18	14.40
XY-0.8-18A41-G	18	13.60	14.58	14.98	15.20
XY-0.8-19A41-G	19	14.40	15.38	15.78	16.00
XY-0.8-20A41-G	20	15.20	16.18	16.58	16.80



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 0.80 Pitch C型WTB刺破型公头	
.X±0.5	X.*±1°	CHK.	Jack	DWG NO. XY-0.8-NA41-G	
.XX±0.2		DRA.	Can	PROJ. CUSTOMER DRAWING	
.XXX±0.1		SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A