





序号	品名	材质
①	0.8-C型卧式WTB底座	LCP UL94 V-0 自然色
②	0.8-C型立式WTB端子	铜合金/表面镀锡
③	0.8-C型卧式WTB焊片	铜合金/表面镀锡
④	0.8-C型立式WTB焊盘	LCP UL94 V-0 黑色




Part No	CKT	A	B
XY-0.8-2A51	2	0.80	3.80
XY-0.8-3A51	3	1.60	4.60
XY-0.8-4A51	4	2.40	5.40
XY-0.8-5A51	5	3.20	6.20
XY-0.8-6A51	6	4.00	7.00
XY-0.8-7A51	7	4.80	7.80
XY-0.8-8A51	8	5.60	8.60
XY-0.8-9A51	9	6.40	9.40
XY-0.8-10A51	10	7.20	10.20
XY-0.8-11A51	11	8.00	11.00
XY-0.8-12A51	12	8.80	11.80
XY-0.8-13A51	13	9.60	12.60
XY-0.8-14A51	14	10.40	13.40
XY-0.8-15A51	15	11.20	14.20

Part No	CKT	A	B
XY-0.8-16A51	16	12.00	15.00
XY-0.8-17A51	17	12.80	15.80
XY-0.8-18A51	18	13.60	16.60
XY-0.8-19A51	19	14.40	17.40
XY-0.8-20A51	20	15.20	18.20
XY-0.8-21A51	21	16.00	19.00
XY-0.8-22A51	22	16.80	19.80
XY-0.8-23A51	23	17.60	20.60
XY-0.8-24A51	24	18.40	21.40
XY-0.8-25A51	25	19.20	22.20
XY-0.8-26A51	26	20.00	23.00
XY-0.8-27A51	27	20.80	23.80
XY-0.8-28A51	28	21.60	24.60

技术指标:

1. 塑料表面应光滑, 无毛边, 无明显收缩, 缺陷, 裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$.
3. 额定电压: 30V AC/DC.
4. 耐压: 200V AC/minute.
5. 接触电阻: $\leq 0.02\Omega$.
6. 绝缘电阻: $\geq 100M\Omega$.
7. 额定电流: 0.5A AC/DC.



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.5	X.*±1°	APR. Alex	TITLE: 0.80 Pitch C型WTB		
.XX±0.2		CHK. Jack	DWG NO. XY-0.8-NA51		
.XXX±0.1		DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1/1