






技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. 额定电压: 250V AC, DC.
3. 耐电压: 800V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$.
5. 绝缘电阻: $\geq 1000\text{M}\Omega$.
6. 额定电流: 3A AC, DC.

材料

1. 塑胶: PA66 白色

型号	CKT	A	B	C
XY-PHB2.0-4A41-G	2*2	2.00	7.00	2.90
XY-PHB2.0-6A41-G	2*3	4.00	9.00	3.10
XY-PHB2.0-8A41-G	2*4	6.00	11.00	4.30
XY-PHB2.0-10A41-G	2*5	8.00	13.00	6.30
XY-PHB2.0-12A41-G	2*6	10.00	15.00	8.30
XY-PHB2.0-14A41-G	2*7	12.00	17.00	6.30
XY-PHB2.0-16A41-G	2*8	14.00	19.00	8.30
XY-PHB2.0-18A41-G	2*9	16.00	21.00	14.30
XY-PHB2.0-20A41-G	2*10	18.00	23.00	14.30
XY-PHB2.0-22A41-G	2*11	20.00	25.00	14.30
XY-PHB2.0-24A41-G	2*12	22.00	27.00	14.30
XY-PHB2.0-26A41-G	2*13	24.00	29.00	14.30
XY-PHB2.0-28A41-G	2*14	26.00	31.00	14.30
XY-PHB2.0-30A41-G	2*15	28.00	33.00	14.30
XY-PHB2.0-32A41-G	2*16	30.00	35.00	14.30
XY-PHB2.0-44A41-G	2*22	42.00	47.00	14.30

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE: PHB2.0 44芯		
.X $\pm$ 0.3	X.* $\pm$ 5°	Alex	DWG NO. XY-PHB2.0-NA41-G		
.XX $\pm$ 0.25	.X.* $\pm$ 1°	CHK. Jack	PROJ.  CUSTOMER DRAWING		
.XXX $\pm$ 0.15		DRA. Can	SIZE A4	SCALE 1:1	SHEET 1/1 REV. A