






Technical Index:

1. Temperature range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
2. Rated voltage: 250V DC/AC.
3. Rated current: 3.0A DC/AC.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Dielectric withstanding voltage: 800V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.
7. Apply to gauge: AWG#24~#28.

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd							
TOLERANCE UNLESS OTHERWISE SPECIFIED									
.X±0.3	X.*± 5°	APR.	Alex	TITLE: PHB2.0端子					
.XX±0.25	.X.*± 1°	CHK.	Jack	DWG NO. XY-PHB2.0-31-G					
.XXX±0.15		DRA.	Can	PROJ. 		CUSTOMER DRAWING			
				SIZE A4	SCALE 1:1	SHEET 1/1	REV. A		