





技术指标:

1. 温度范围: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. 额定电压: 150V AC, DC.
3. 耐电压: 500V AC/minute.
4. 接触电阻: $\leq 20\text{m}\Omega$ (Initial) per contact, $\leq 40\text{m}\Omega$ Change allowed.
5. 绝缘电阻: $\geq 500\text{M}\Omega$.
6. 额定电流: 1A AC, DC.

材质:

1. 塑胶: PA66



型号	CKT	A	B	C
XY-DF1.25-10A41-G	2*5	10.50	5.00	7.86
XY-DF1.25-12A41-G	2*6	11.75	6.25	9.11
XY-DF1.25-14A41-G	2*7	13.00	7.50	10.36
XY-DF1.25-16A41-G	2*8	14.25	8.75	11.61
XY-DF1.25-18A41-G	2*9	15.50	10.00	12.86
XY-DF1.25-20A41-G	2*10	16.75	11.25	14.11
XY-DF1.25-22A41-G	2*11	18.00	12.50	15.36
XY-DF1.25-24A41-G	2*12	19.25	13.75	16.61
XY-DF1.25-28A41-G	2*14	21.75	16.25	19.11
XY-DF1.25-30A41-G	2*15	23.00	17.50	20.36
XY-DF1.25-32A41-G	2*16	24.25	18.75	21.61
XY-DF1.25-34A41-G	2*17	25.50	20.00	22.86
XY-DF1.25-36A41-G	2*18	26.75	21.25	24.11
XY-DF1.25-38A41-G	2*19	28.00	22.50	25.36
XY-DF1.25-40A41-G	2*20	29.25	23.75	26.61
XY-DF1.25-42A41-G	2*21	30.50	25.00	27.86
XY-DF1.25-44A41-G	2*22	31.75	26.25	29.11
XY-DF1.25-46A41-G	2*23	33.00	27.50	30.36
XY-DF1.25-48A41-G	2*24	34.25	28.75	31.61
XY-DF1.25-50A41-G	2*25	35.50	30.00	32.86

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 1.25 Pitch A型(DF13)双排A型	
.X $\pm$ 0.3	X.* $\pm$ 5°	CHK.	Jack	DWG NO. XY-DF1.25-N41-G	
.XX $\pm$ 0.25	.X.* $\pm$ 1°	PROJ.	Can	CUSTOMER DRAWING	
.XXX $\pm$ 0.15		SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A