

A





B

C

D


E

F



技术指标(Technical Index):

- 1.工作温度(Temperature range):
-40°C~+105°C.
- 2.额定电压(Rated voltage):250V DC/AC(rms).
- 3.额定电流(Rated current):3.0A AC,DC.
- 4.接触电阻(Contact resistance):≤20mΩ.
- 5.耐压值(Dielectricwithstanding voltage):
800V AC/minute.
- 6.绝缘电阻(Insulation resistance):≥1000MΩ.



序号	① 品名	材质
	PHD2.0直针WTB嵌芯	PA66+玻纤
	PHD2.0直针WTB端子	UL94 V-0 米色
		铜合金/表面镀锡

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.5	X.*± 1°	APR. Alex	TITLE: PHD2.0 双排直插WTB				
.XX±0.2		CHK. Jack	DWG NO. XY-PHD2.0-2-NA11				
.XXX±0.1		DRA. Can	PROJ. 		CUSTOMER DRAWING		
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A	

A

B

C

D

E

F