

ELECTRICAL:





1. VOLTAGE RATING: 125 VAC RMS
2. CURRENT RATING: 1.5 AMP
3. CONTACT RESISTANCE: 30mΩ MAX.
4. INSULATION RESISTANCE: 500MΩMIN. AT 500V DC.
5. DIELECTRIC STRENGTH: 1000 VAC 50Hz 1MINUTE

MECHANICAL:



1. HOUSING MATERIAL:
SEE PART NUMBER.
2. CONTACTS: 0.46mm PHOSPHOR BRONZE, GOLD
PLATING OVER NICKEL
3. SHIELD: 0.20mm THICKNESS COPPER ALLOY WITH
NICKEL PLATED.
4. OPERATING LIFE: 750 CYCLES MIN.
5. MATING FORCE: 22N MAX.
UNMATING FORCE: 22N MAX.
6. Wave soldering Temp.: 235°+/-5°

ENVIRONMENTAL:

1. STORAGE: -40°C TO +85°C
2. OPERATION: -40°C TO +85°C



Recommend PCB Layout
TOLERANCES: $\pm 0,05$



UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:		ANGLES:	
X	:±0.35	X	:±2°
X.X	:±0.25	X.X	:±1°
X.XX	:±0.15		



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	RJ45 5224 8P8C 全包帶灯 左绿右黄脚厚3.85			
DWN	xiong	PART NO. RJ45-5211881B15-B		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4
CUSTOMER COPY				