




REV.	Q'TY	ECN. NO.	APR.	DATE






序号	品名	材质
①	PHD贴片WTB胶芯	LCP UL94V-0本色
②	PHD贴片(连续)端子	铜合金/表面镀锡

Part No	Pin	A	B
XY-PHD2.0-4A61	2*2	2.00	6.00
XY-PHD2.0-6A61	2*3	4.00	8.00
XY-PHD2.0-8A61	2*4	6.00	10.00
XY-PHD2.0-10A61	2*5	8.00	12.00
XY-PHD2.0-12A61	2*6	10.00	14.00
XY-PHD2.0-14A61	2*7	12.00	16.00
XY-PHD2.0-16A61	2*8	14.00	18.00
XY-PHD2.0-18A61	2*9	16.00	20.00
XY-PHD2.0-20A61	2*10	18.00	22.00
XY-PHD2.0-22A61	2*11	20.00	24.00
XY-PHD2.0-24A61	2*12	22.00	26.00
XY-PHD2.0-26A61	2*13	24.00	28.00
XY-PHD2.0-28A61	2*14	26.00	30.00
XY-PHD2.0-30A61	2*15	28.00	32.00
XY-PHD2.0-32A61	2*16	30.00	34.00
XY-PHD2.0-36A61	2*18	34.00	38.00
XY-PHD2.0-40A61	2*20	38.00	42.00

技术指标(Technical Index):

- 1.工作温度(Temperature range):-40°C~+105°C.
- 2.适用线规(Apply to gauge):AWG#28~#24
- 3.额定电压(Rated voltage):250V DC/AC(rms).
- 4.额定电流(Rated current):3.0A AC,DC.
- 5.接触电阻(Contact resistance):≤20mΩ.
- 6.耐压值(Dielectricwithstanding voltage):800V AC/minute.
- 7.绝缘电阻(Insulation resistance):≥1000MΩ.

SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.25	X.*± 3°	APR.	Alex	TITLE: 2.0 Pitch D型连接器			
.XX±0.12	.X*± 0.5°	CHK.	Jack	DWG NO. XY-PHD2.0-NA61			
.XXX±0.05				PROJ.		CUSTOMER DRAWING	
			Can	SIZE A4	SCALE 1:1	SHEET 1/1	REV. A