

REV.	Q'TY	ECN. NO.	APR.	DATE

序号	品名	材质
①	0.8-C型WTB 刺破型公头胶芯	PA66+玻纤 UL94 V-0 米黄色
②	0.8-C型WTB 刺破型公头端子	铜合金/镀金

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$ (含通电时的温度上升值)。
3. 额定电压: 30V, AC/DC。
4. 接触电阻: 初期 $\leq 0.02\Omega$, 环境试验后 $\leq 0.04\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ min。
6. 额定电流: 0.5A, AC/DC
(使用AWG#32, $0.0038\pm 0.02\text{mm}$)。
7. 耐电压: AC 200V/1分钟。

Part No	CKT	A	B	C	D
XY-0.8-2A41-CP	2	0.80	1.78	2.18	2.40
XY-0.8-3A41-CP	3	1.60	2.58	2.98	3.20
XY-0.8-4A41-CP	4	2.40	3.38	3.78	4.00
XY-0.8-5A41-CP	5	3.20	4.18	4.58	4.80
XY-0.8-6A41-CP	6	4.00	4.98	5.38	5.60
XY-0.8-7A41-CP	7	4.80	5.78	6.18	6.40
XY-0.8-8A41-CP	8	5.60	6.58	6.98	7.20
XY-0.8-9A41-CP	9	6.40	7.38	7.78	8.00
XY-0.8-10A41-CP	10	7.20	8.18	8.58	8.80
XY-0.8-11A41-CP	11	8.00	8.98	9.38	9.60
XY-0.8-12A41-CP	12	8.80	9.78	10.18	10.40
XY-0.8-13A41-CP	13	9.60	10.58	10.98	11.20
XY-0.8-14A41-CP	14	10.40	11.38	11.78	12.00
XY-0.8-15A41-CP	15	11.20	12.18	12.58	12.80
XY-0.8-16A41-CP	16	12.00	12.98	13.38	13.60
XY-0.8-17A41-CP	17	12.80	13.78	14.18	14.40
XY-0.8-18A41-CP	18	13.60	14.58	14.98	15.20
XY-0.8-19A41-CP	19	14.40	15.38	15.78	16.00
XY-0.8-20A41-CP	20	15.20	16.18	16.58	16.80

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.3	X.*±1°	APR.	Alex	TITLE: 0.80 Pitch C型WTB刺破型公头			
.XX±0.2		CHK.	Jack	DWG NO. XY-0.8-NA41-CP			
.XXX±0.1		DRA.	Can	PROJ. 		CUSTOMER DRAWING	
				SIZE A4	SCALE 1:1	SHEET 1/1	REV. A