




技术指标(Technical Index):

1. 工作温度(Temperature range): $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$.
2. 额定电压(Rated voltage): 30V AC/DC.
3. 额定电流(Rated current): 0.5A AC/DC.
4. 接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
5. 耐压值(Dielectric withstanding voltage): 200V AC/minute.
6. 绝缘电阻(Insulation resistance): $\geq 100\text{M}\Omega$.
7. 适用线规(Apply to gauge): AWG#28~#32(0.006mm MAX).

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd					
TOLERANCE UNLESS OTHERWISE SPECIFIED							
.X±0.3	X.*±1*	APR.	Alex	TITLE: 0.80 Pitch C型WTB系列			
.XX±0.2		CHK.	Jack	DWG NO. XY-0.8-31-G			
.XXX±0.1		DRA.	Can	PROJ. 		CUSTOMER DRAWING	
				SIZE A4	SCALE 1:1	SHEET 1/1	REV. A