







HAOYU

1. 额定电负荷：DC 30V 0.5A；
2. 接触电阻： $\leq 0.06\Omega$ ；
3. 绝缘电阻： $\geq 100M\Omega$ (DC250V)；
4. 耐压：500VAC
5. 插力：3-30N
6. 拔力：3-30N
7. 寿命：5,000



(ø3.50mm 4 POLE PLUG DETAIL DRAWING)



线路板开孔尺寸

SCHEMATIC

PJ-392A	PJ-392A-1	PJ-392A-2	PJ-392A-3	PJ-392A-4	PJ-392A-5	PJ-392A-6	PJ-392A-7	PJ-392A-8	PJ-392A-9	PJ-392A-10	PJ-392A-11

9	PJ392B 底座	PA46	1	BLACK	TOLERANCE UNLESS SPECIFIED UP TO 5mm:±0.1 ANGULAR ABOVE 5mm:±0.2 ±1° A1 2021.11.30 A0 2021.04.23 NO DATE 更新BOM信息 首次发行 REVISIONS GYW GYW BY APPD										
8	PJ392A 4#弹片	SUS301	1	Ag-PLATED											
7	PJ392A 2#接触片	BRASS	1	AU-PLATED											
6	PJ392A 2#接触片	BRASS	1	AU-PLATED											
5	PJ392A 3#接触片	BRASS	1	AU-PLATED											
4	PJ392A 1#接触片	BRASS	1	AU-PLATED	TITLE: PHONE JACK				UNIT : MM	ROHS	DWN				
3	PJ392A 5#弹片	SUS301	1	AU-PLATED	MODEL: PJ-392A(HY)				SCALE: 3:1	COMPLIANT	CHK'D				
2	PJ392A 5#弹片	SUS301	1	AU-PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司								APPD		
1	PJ392A 5#弹片	SUS301	1	AU-PLATED									PRO.AGL:		REV :A1
NO.	PART NAME	MATERIAL	QTY	FINISHING											