




序号	品名	材质
①	0.6-卧式WTB胶芯	LCP UL94 V-0 黑色
②	0.6-卧式WTB端子	铜合金/表面镀锡
③	0.6-卧式WTB焊片	铜合金/表面镀锡

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 105^{\circ}\text{C}$.
3. 额定电压: 30V, AC/DC.
4. 耐电压: 200V, AC/minute.
5. 接触电阻: $\leq 0.02\Omega$.
6. 绝缘电阻: $\geq 100\text{M}\Omega$.
7. 额定电流: 0.5A AC/DC.



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.5	X.*±1°	APR. Alex	TITLE: 0.60 Pitch 卧式WTB			
.XX±0.2		CHK. Jack	DWG NO. XY-0.6-NA61			
.XXX±0.1		DRA. Can	PROJ. 		CUSTOMER DRAWING	
			SIZE A4	SCALE 1:1	SHEET 1/1	REV. A

Part No	CKT	A	B	C
XY-0.6-2A61	2	0.60	1.40	3.10
XY-0.6-3A61	3	1.20	2.00	3.70
XY-0.6-4A61	4	1.80	2.60	4.30
XY-0.6-5A61	5	2.40	3.20	4.90
XY-0.6-6A61	6	3.00	3.80	5.50
XY-0.6-7A61	7	3.60	4.40	6.10
XY-0.6-8A61	8	4.20	5.00	6.70
XY-0.6-9A61	9	4.80	5.60	7.30
XY-0.6-10A61	10	5.40	6.20	7.90
XY-0.6-11A61	11	6.00	6.80	8.50
XY-0.6-12A61	12	6.60	7.40	9.10
XY-0.6-13A61	13	7.20	8.00	9.70
XY-0.6-14A61	14	7.80	8.60	10.30
XY-0.6-15A61	15	8.40	9.20	10.90
XY-0.6-16A61	16	9.00	9.80	11.50
XY-0.6-17A61	17	9.60	10.40	12.10
XY-0.6-18A61	18	10.20	11.00	12.70
XY-0.6-19A61	19	10.80	11.60	13.30
XY-0.6-20A61	20	11.40	12.20	13.90
XY-0.6-21A61	21	12.00	12.80	14.50
XY-0.6-22A61	22	12.60	13.40	15.10