





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTES:

- 1.Rated voltage: 300V AC.DC
- 2.Rated current: 8A AC DC
- 3.Contact resistance: $\leq 20\text{ m}\Omega$
- 4.Insulation resistance: $\geq 500\text{ M}\Omega$
- 5.Withstand voltage: 1500V AC/minute
- 6.Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
- 7.Material: Nylon UL94V-0
- 8.Pin Material: Brass/Nickel Plated



PCB LAYOUT

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司		
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD		
CHECK					
APPROVAL					
TOLERANCES ARE			TITLE	插拔式接线端子PIN距3.81（4P）直插	REV. A
30-150	±0.35	ANGLE	PART NO.	LAIL-PTB3.81-4P-GN-01-ZC	UNITS mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
		±3°	DWG.NO.		Projection 