




ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTES:

- 1.Rated voltage: 300V AC/DC
- 2.Rated current: 8A AC DC
- 3.Contact resistance: $\leq 20\text{ m}\Omega$
- 4.Insulation resistance: $\geq 500\text{ M}\Omega$
- 5.Withstand voltage: 1500V AC/minute
- 6.Ambient temprature: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
- 7.Material: Nylon UL94V-0
- 8.Pin Material: Brass/Nickel Plated



PCB LAYOUT

COSTOMER DRAWING				LAILIAN 深圳市莱联电子有限公司								
DRAWING				SHENZHEN LAILIAN ELECTRONICS CO., LTD								
CHECK												
APPROVAL												
TOLERANCES ARE				TITLE		插拔式接线端子PIN距3.81（5P）弯插		REV.		A		
30-150		±0.35		ANGLE	PART NO.		LAIL-PTB3.81-5P-GN-01-WC		UNITS		mm	
10-30		±0.2										
5-10		±0.15										
0-5		±0.1										
				±3°	DWG.NO.				Projection			