








PCB Layout(Pattern side)



U型脚款 K2-1157UX-A□□W-□□




PCB Layout(Pattern side)



NO.1	
PART NO	vigor
4	250±30
6	400±60

NO.2	
PART NO	MATERIAL/QTY
S	SUS/1PC

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER



Circuit Diagram

⑤	Terminal	—	4	Brass	Plating silver	—
④	Contact	—	1	F.Ag/SUS	Natural	—
③	Base	—	1	PPA	Black	—
②	Cover	—	1	SPCC	—	—
①	Keystoke	—	1	Silica gel	Red	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		 hro®			
DRAWN		LIUCAN	2023.10.30					
CHECKED					TITLE:	TACT SWITCHES		
APPROVALS					PART NO.	K2-1157SX-A□□W-□□		
D.	TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
			10~30	±0.20				
			5~10	±0.15				
			~ 5	±0.10				
			±2°		DRAWING NO.	_____		SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.