




ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTES:

- 1.Rated voltage: 300V AC.DC
- 2.Rated current: 15A AC DC
- 3.Contact resistance: $\leq 20\text{ m}\Omega$
- 4.Insulation resistance: $\geq 500\text{ M}\Omega$
- 5.Withstand voltage: 2000V AC/minute
- 6.Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
- 7.Material: Nylon UL94V-0
- 8.Pin Material: Brass/Nickel Plated



PCB LAYOUT

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
CHECK							
APPROVAL							
TOLERANCES ARE			TITLE		插拔式接线端子PIN距5.08 (8P)弯插	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PTB5.08-8P-GN-01-WC	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			DWG.NO.		Projection		