







P.C.B layout



Schematic(Shorting)

NO.1	
PART NO	H
K3-2501S-G2	2.0
K3-2501S-G4	4.0

⑤	Contact	—	2	Beryllium bronze	Ag Plated	—
④	Terminal	—	14	Brass Strip	Ag Plated	—
③	Base	—	1	LCP	Black	—
②	Cover	—	1	Steel	—	—
①	Knob	—	1	NYLON	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE			
DRAWN		LIUCAN	2023.10.25			
CHECKED					TITLE:	TOGGLE SWITCHES
APPROVALS					PART NO.	K3-2501S-G 
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
	10~30	±0.20				
	5~10	±0.15				
	~ 5	±0.10				
		±2'	DRAWING NO.	_____	SHEET 1 OF 1	

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.