




PCB Layout (Pattern side)

Circuit Diagram



- Typical Specifications :
1. Rating : DC 12V 100mA
 2. Life:10,000 Cycles

PART NO.	L	Operating force
K3-1346F-F1	2	200±50gf
K3-1346F-K1	3	
K3-1346F-L1	4	

⑤	Contact Spring	—	2	Beryllium copper	Ag Plated	—
④	Terminal	—	4	Phosphor bronze	Ag Plated	—
③	Base	—	1	NYLON	Black	—
②	Cover	—	1	SUS	Natural	—
①	KNOB	—	1	NYLON	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	

APPROVALS			DATE				
DRAWN	LIUCAN	2020.12.10					
CHECKED				TITLE:	TOGGLE SWITCHES		
APPROVALS				PART NO.			
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2'	DRAWING NO.	_____	SHEET 1 OF 1	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			