





Circuit Diagram



PCB Layout(Pattern Side)

NO.1—NO.2	
PART NO	NOTE
01~99	SERIAL NUMBER

Typical Specifications :

- Rating : DC 12V 50mA
- Operating force: 160±50gf
- Life:100,000 Cycles Min.

⑤	Terminal	—	2	Phosphor Bronze	Plating silver	—
④	Contact	—	2	F.Ag/SUS	—	—
③	Base	—	1	LCP	White	—
②	Cover	—	1	Phosphor Bronze	Plating silver	—
①	Keystoke	—	1	LCP	White	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS				DATE		 hro®	
DRAWN		LIUCAN		2025.4.18			
CHECKED						TITLE: TACT SWITCHS	
APPROVALS						PART NO. K2-1806FQ-A3DW-□□	
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.20		DRAWING NO.		SHEET 1 OF 1
		5~10	±0.15				
		~ 5	±0.10				

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.