





ROHS



NOTE:
1.Rated voltage: 300V AC.DC
2.Rated current: 15A AC.DC
3.Contact Resistance: 20mΩ Max
4.Insulation Resistance: 500MΩ Min
5.Withstanding Voltage: 2000V AC/minute
6.Ambient temperature: -40℃to+105℃
7.Material: Nylon UL94V-0

5	盖板	PA66 UL94V-0	1	绿色			
4	压线框	黄铜	5	镀镍			
3	夹片	磷青铜	5	镀镍			
2	基座	PA66 UL94V-0	1	绿色			
1	螺钉	钢	5	镀锌	M2. 5		
序号	名称	材质	数量	电镀/颜色	备注		
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司					
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD					
CHECK							
APPROVAL							
TOLERANCES ARE		TITLE	插拔式接线端子PIN距5.08 (5P)公插头		REV. A		
30-150	±0.35	PART NO.	LAIL-PTB5.08-5P-GN-01-MC	UNITS	mm		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
ANGLE		DWG.NO.		Projection 			
±3°							