





ROHS



## NOTES:

- 1.Rated voltage: 300V AC.DC
- 2.Rated current: 8A AC DC
- 3.Contact resistance:  $\leq 20 \text{ m}\Omega$
- 4.Insulation resistance:  $\geq 500 \text{ M}\Omega$
- 5.Withstand voltage: 1500V AC/minute
- 6.Ambient temprature:  $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
- 7.Material: Nylon UL94V-0
- 8.Pin Material: Brass/Nickel Plated



## PCB LAYOUT

|                  |  |                                       |  |            |  |
|------------------|--|---------------------------------------|--|------------|--|
| COSTOMER DRAWING |  | LAILIAN 深圳市莱联电子有限公司                   |  |            |  |
| DRAWING          |  | SHENZHEN LAILIAN ELECTRONICS CO., LTD |  |            |  |
| CHECK            |  |                                       |  |            |  |
| APPROVAL         |  |                                       |  |            |  |
| TOLERANCES ARE   |  | TITLE                                 |  | REV. A     |  |
| 30-150 ±0.35     |  | PART NO.                              |  | UNITS mm   |  |
| 10-30 ±0.2       |  | LAIL-PTB3.81-5P-GN-01-ZC              |  |            |  |
| 5-10 ±0.15       |  | DWG.NO.                               |  | Projection |  |
| 0-5 ±0.1         |  |                                       |  | ④          |  |
| ANGLE ±3°        |  |                                       |  |            |  |