





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTES:

- 1.Rated voltage: 300V AC.DC
- 2.Rated current: 15A AC DC
- 3.Contact resistance: $\leq 20\text{ m}\Omega$
- 4.Insulation resistance: $\geq 500\text{ M}\Omega$
- 5.Withstand voltage: 2000V AC/minute
- 6.Ambient temprature: $-40^{\circ}\text{C}\sim +105^{\circ}\text{C}$
- 7.Material: Nylon UL94V-0
- 8.Pin Material: Brass/Nickel Plated



PCB LAYOUT

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD					
DRAWING							
CHECK							
APPROVAL							
TOLERANCES ARE		TITLE	插拔式接线端子PIN距5.08 (3P) 弯插带螺母	REV.	A		
30-150	±0.35	PART NO.	LAIL-PTB5.08-3P-GN-03S-WC	UNITS	mm		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
ANGLE		DWG.NO.		Projection			
±3°							