


ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- NOTES:
- 1.Rated voltage: 300V AC.DC
 - 2.Rated current: 8A AC DC
 - 3.Contact resistance: ≤20 mΩ
 - 4.Insulation resistance: ≥500 MΩ
 - 5.Withstand voltage: 1500V AC/minute
 - 6.Ambient temprature: -40℃~+105℃



5	盖板	PA66 UL94V-0	1	绿色	
4	压线框	黄铜	2	镀镍	
3	夹片	磷青铜	2	镀镍	
2	基座	PA66 UL94V-0	1	绿色	
1	螺钉	钢	2	镀锌	M2
序号	名称	材质	数量	电镀/颜色	

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司		
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD		
CHECK					
APPROVAL					
TOLERANCES ARE			TITLE	插拔式接线端子PIN距3.81 (2P)公插头带螺钉	REV. A
30-150	±0.35	ANGLE	PART NO.	LAIL-PTB3. 81-2P-GN-01S-MC	UNITS mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
DWG.NO.			Projection 		