





Circuit Diagram



PCB Layout(Pattern side)



Rated: DC12V 50mA
IP Rating: IP67

NO.1			
PART NO	vigor	Keystoke	Life time
5	320±50	Blue	150,000 Cycles
6	420±50	Red	100,000 Cycles
7	620±50	Green	50,000 Cycles

NO.2-NO.3	
PART NO	NOTE
01~99	SERIAL NUMBER

⑤	Terminal	—	4	Brass(0.3t)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	—	—
③	Base	—	1	PPA	Black	—
②	Cover	—	1	PPA	Black	—
①	Keystoke	—	1	Silica gel	—	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE				
DRAWN	LIUCAN	2024.6.5		TITLE: TACT SWITCHS		
CHECKED				PART NO. K2-6547SP-B□SW-□□		
APPROVALS				UNIT: mm SCALE: 1:1 PROJ:		
TOLERANCES ARE		30~以上	±0.30	ANGLE	DRAWING NO.	SHEET 1 OF 1
		10~30	±0.20			
		5~10	±0.15			
		~ 5	±0.10			

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.