




Circuit diagram

NOTE:
Rating:DC 12V 50mA
Contact resistance:100mΩ Max
Life: 100,000 Cycles
IP Rating: IP67



NO.1	
PART NO	H
A	3.8
C	4.5
D	5

NO.2	
PART NO	vigor
3	180±30
4	250±50

NO.3—NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

⑦	Waterproof Pad	—	1	Silica gel	Black	—
⑥	Membrane	—	1	PI	Yellow	—
⑤	Terminal	—	2	Brass(0.30t)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	—	—
③	Base	—	1	PPA	Black	—
②	Cover	—	1	Brass	Plating Sn	—
①	Keystoke	—	1	PPA	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE					
DRAWN		LIUCAN	2025.7.11					
CHECKED					TITLE:	TACT SWITCHS		
APPROVALS					PART NO.	K2-1109SH-□□SW-□□		
TOLERANCES ARE			30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
			10~30	±0.20				
			5~10	±0.15				
			~ 5	±0.10				
			±2°		DRAWING NO.	_____		SHEET 1 OF 1

	A		NEW			
ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.