





ROHS



NOTES:

- 1.Rated voltage: 300V AC.DC
- 2.Rated current: 8A AC DC
- 3.Contact resistance: $\leq 20 \text{ m}\Omega$
- 4.Insulation resistance: $\geq 500 \text{ M}\Omega$
- 5.Withstand voltage: 1500V AC/minute
- 6.Ambient temprature: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
- 7.Material: Nylon UL94V-0

5	盖板	PA66 UL94V-0	1	绿色	
4	压线框	黄铜	10	镀镍	
3	夹片	磷青铜	10	镀镍	
2	基座	PA66 UL94V-0	1	绿色	
1	螺钉	钢	10	镀锌	M2
序号	名称	材质	数量	电镀/颜色	备注

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司				
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE		插拔式接线端子PIN距3.81 (10P) 公插头	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PTB3.81-10P-GN-01-MC	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
DWG.NO.				Projection		