





ROHS



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:
1.Rated voltage: 300V AC.DC
2.Rated current: 15A AC.DC
3.Contact Resistance: 20mΩ Max
4.Insulation Resistance: 500MΩ Min
5.Withstanding Voltage: 2000V AC/minute
6.Ambient temperature: -40℃to+105℃
7.Material: Nylon UL94V-0

5	盖板	PA66 UL94V-0	1	绿色	
4	压线框	黄铜	8	镀镍	
3	夹片	磷青铜	8	镀镍	
2	基座	PA66 UL94V-0	1	绿色	
1	螺钉	钢	8	镀锌	M2.5
序号	名称	材质	数量	电镀/颜色	备注

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司				
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE	插拔式接线端子PIN距5.08 (8P)公插头	REV.	A	
30-150	±0.35	PART NO.	LAIL-PTB5.08-8P-GN-01-MC	UNITS	mm	
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
ANGLE		DWG.NO.		Projection 		
±3°						