

F




E

D

C

B

A



Ordering Information

C SCC118 - XX

XX

A

002

C

X

A

X

No. of Pins per Row
02~40Standard Plating
02=Gold Flash
Selective Plating
01=Tin
05=Gold Flash/TinColor
1=Black
E=BeigeStandard Packing
C=Tube
Selective Packing
A=box
E=Cap+Tube
F=Cap+Tape&Reel
G=Acetate Tape+Tube
H=Acetate Tape+Tape&Reel
D=Tape+Reel

REV.	LOCAS.	DESCRIPTION	DATE	DRAWN
04	△	以防止膠紙脫落, 變更02~40pin膠紙規格	2012.08.24	黃小燕
05	△	Layout錯誤更正Layout	2013.11.22	李芳忠
06	△	依業務要求增加米色塑膠	2017.06.19	馮國東
07	△	Added D=Tape+Reel packing	2022.08.26	郭 康
08	△	Added P.C.B LAYOUT FOR BOTTOM ENTRY	2024.08.28	郭 康

Specifications

Current Rating:1Amp

Insulation Resistance:1000MΩMin.


Dielectric Withstanding Voltage:300VAC

△ Contact Resistance:20mΩMax.

Operating Temperature:-40°C to +105°C
Materials△ Contact Material:Phosphor Bronze
Insulator Material:High Temperature
Thermoplastic, UL 94V-0 LCP or the
equivalent materialAll materials must meet Greenconn
hazardous substances control standards.


Recommended P.C.Board Layout

(Tolerance:±0.05)




RECOMMENDED P.C.B LAYOUT FOR BOTTOM ENTRY

(Tolerance:±0.05)



REV. 08 UNIT. mm SCALE. 5:1

3RD.ANG
PROJ.

PAGE. 1/1

GENERAL TOLERANCE

X.*±5.0°	X.±0.30
.X.*±3.0°	.X.±0.25
.XX.*±2.0°	.XX±0.15
.XXX.*±1.0°	.XXX±0.10

DESIGNED: 郭 康

DATE: 2024.08.28

CHECKED: 張春進

DATE: 2024.08.28

APPROVED: 邱國延

DATE: 2024.08.28

DWG. NO.

CSCC118-CA2CA

PART NO.

CSCC118-XXXX A002CXAX

TITLE.

1.00 FEMALE HEADER
SINGLE ROW SMT TYPE
CONNECTOR

F

E

D

C

B

A