




ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTES:

- 1.Rated voltage: 300V AC.DC
- 2.Rated current: 15A AC DC
- 3.Contact resistance: ≤20 mΩ
- 4.Insulation resistance: ≥500 MΩ
- 5.Withstand voltage: 2000V AC/minute
- 6.Ambient temprature: -40℃~+105℃
- 7.Material: Nylon UL94V-0
- 8.Pin Material: Brass/Nickel Plated



PCB LAYOUT

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE	插拔式接线端子PIN距5.08（4P）弯插	REV.	A	
30-150	±0.35	ANGLE	PART NO.	LAIL-PTB5.08-4P-GN-01-WC	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
		DWG.NO.		Projection		