







PCB Layout(Pattern side)



Circuit Diagram

NOTE:
Rating:DC 12V 50mA
Contact resistance:100mΩ Max
Operating force:400±100gf
Operation life:1,000,000 Cycles

⑤	Terminal	—	4	Phosphor bronze	Plating silver	—
④	Contact	—	1	F.Au/SUS	—	—
③	Base	—	1	PPA	Black	—
②	Cover	—	1	PPA	Black	—
①	Keystoke	—	1	Silica gel	Transparent	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE					
DRAWN	LIUCAN	2024.11.9						
CHECKED				TITLE:	TACT SWITCHS			
APPROVALS					PART NO.	K2-1841SQ-C5SW-□□		
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
		10~30	±0.20					
		5~10	±0.15					
		~ 5	±0.10					
		±2°		DRAWING NO.	_____		SHEET 1 OF 1	

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.