





NO.1	
PART NO	H
A	3.8
B	4.3
C	4.5
D	5

NO.2	
PART NO	vigor
3	160±30
4	250±50

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

NOTE:
Rating: DC 12V 50mA
Contact resistance: 100mΩ Max
Life: 100,000 Cycles
IP Rating: IP67

⑦	Waterproof Pad	—	1	Silica gel	Black	—
⑥	Membrane	—	1	PI	Yellow	—
⑤	Terminal	—	2	Brass(0.30t)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	—	—
③	Base	—	1	PPA	Black	—
②	Cover	—	1	PPA	Black	—
①	Keystoke	—	1	PPA	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE					
DRAWN	LIUCAN	2024.6.29					
CHECKED				TITLE:	TACT SWITCHES		
APPROVALS				PART NO.	K2-1109EG-□□SW-□□		
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
		10~30	±0.20				
		5~10	±0.15				
		~ 5	±0.10				
		±2'		DRAWING NO.			SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.