





NOTE:

1. Rate voltage.current: 50mA DC12V
2. Contact resistance: $\leq 100\text{m}\Omega$
3. Operating force: $\pm 50\text{gf}$
4. Insulated resistance: $\geq 100\text{M}\Omega$
5. Dielectric strength: $\geq 250\text{VAC}/1\text{min}$



NO.1	
PART NO	vigor
3	160±50
4	250±50
5	350±50

NO.2	
PART NO	MATERIAL/QTY
D	SUS/2PCS

NO.3-NO.4	
PART NO	NOTE
01~99	SERIAL NUMBER

⑥	Knob	——	1	LCP	Beige	——
⑤	Cover	——	1	Phosphor Bronze	Plating silver	——
④	Dustproof film	——	1	Polyimide	Orange-yellow	——
③	Contact	——	2	SUS	Plating silver	——
②	Base	——	1	LCP	Black	——
①	Terminal	——	3	Phosphor Bronze	Plating silver	——
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE		hro®	
DRAWN	LIANG		2026.3.28			
CHECKED			TITLE:		TACT SWITCHS	
APPROVALS			PART NO.		K2-1812AN-□□□W-□□	
TOLERANCES ARE			30~以上	±0.30	ANGLE	UNIT: mm
			10~30	±0.20		SCALE: 1:1
			5~10	±0.15		PROJ:
			~ 5	±0.10	±2'	DRAWING NO.
					SHEET 1 OF 1	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			