





ROHS



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:

- 1.Rated voltage: 300V AC.DC
- 2.Rated current: 15A AC.DC
- 3.Contact Resistance: 20mΩ Max
- 4.Insulation Resistance: 500MΩ Min
- 5.Withstanding Voltage: 2000V AC/minute
- 6.Ambient temperature: -40℃to+105℃
- 7.Material: Nylon UL94V-0

5	盖板	PA66 UL94V-0	1	绿色	
4	压线框	黄铜	10	镀镍	
3	夹片	磷青铜	10	镀镍	
2	基座	PA66 UL94V-0	1	绿色	
1	螺钉	钢	10	镀锌	M2.5
序号	名称	材质	数量	电镀/颜色	备注

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司					
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD					
CHECK							
APPROVAL							
TOLERANCES ARE		TITLE		插拔式接线端子PIN距5.08（10P）公插头	REV.	A	
30-150	±0.35	PART NO.	LAIL-PTB5.08-10P-GN-01-MC	UNITS	mm		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
ANGLE		DWG.NO.		Projection			
±3°							