




PCB Layout(Pattern side)

Typical Specifications

1.Rating : DC 12V 50mA

2.Contact Resistance: $\leq 100\text{m}\Omega$ 3.Insulation Resistance: $\geq 100\text{m}\Omega$

4.Life : 100,000 Cycles

PART NO.	Circuit Diagram
K2-1110SW	
K2-1110SF	

NO.2	
PART NO	H
A	3.2
B	3.6

NO.3	
PART NO	vigor
3	180±30
4	250±40

NO.4-NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER

⑥	Cover	—	1	Phosphor copper	Tin Plated	—
⑤	Keystoke	—	1	PPA	Brown	—
④	Dustproof film	—	1	PI	Yellow	—
③	Contact	—	1	F.Ag/SUS	Plating silver	—
②	Base	—	1	PPA	Black	—
①	Terminal	—	4	Brass(0.3t)	Plating silver	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE				
DRAWN	LIUCAN	2021.9.23		TITLE:	TACT SWITCHS	
CHECKED				PART NO.	K2-1110S□-□□SW-□□	
APPROVALS				UNIT: mm	SCALE: 1:1	PROJ:
TOLERANCES ARE		30~以上	±0.30	ANGLE	DRAWING NO.	SHEET 1 OF 1
		10~30	±0.20			
		5~10	±0.15	±2'		
		~ 5	±0.10			

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.