






Circuit Diagram



PCB Layout



SPECIFICATION

1. Rating: DC 12V 50mA Max
2. Contact resistance: 100mΩ MAX
3. Insulation resistance: 100MΩ Min
4. Dielectric strength: 250VAC/min
5. Operating force: 400gf±100gf
6. Operating life: 300,000 cycles
7. IP Rating: IP67

5	Cover	—	1	SUS304	—	—
4	Stem	—	1	RUBBER	Orange	—
3	Contact Form	—	1	SUS301	Ag-PLATING	—
2	Housing	—	1	PA6T	Black	—
1	Terminal	—	1	H65	Ag-PLATING	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN		LIANG	2026.03.17				
CHECKED				TITLE:		TACT SWITCHES	
APPROVALS				PART NO.		K2-6262UP	
D. TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
		±2'	DRAWING NO.	_____	SHEET 1 OF 1		

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.