







Circuit Diagram

Note:
Operating force: 170±50gf

⑥	Spring	—	2	SUS	Natural	—
⑤	Contact Spring	—	1	Phosphor bronze	Ag Plated	—
④	Terminal	—	4	Phosphor bronze	Ag Plated	—
③	Base	—	1	LCP	Black	—
②	Cover	—	1	SUS	Natural	—
①	KNOB	—	1	NYLON	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN		J.X.Zhang	2020/7/11				
CHECKED					TITLE:		TOGGLE SWITCHES
APPROVALS					PART NO.		K3-1287S-J1
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2'	DRAWING NO.	_____	SHEET 1 OF 1	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			