





ROHS



NOTES:

- 1.Rated voltage: 300V AC.DC
- 2.Rated current: 8A AC DC
- 3.Contact resistance: $\leq 20 \text{ m}\Omega$
- 4.Insulation resistance: $\geq 500 \text{ M}\Omega$
- 5.Withstand voltage: 1500V AC/minute
- 6.Ambient temprature: $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$

5	盖板	PA66 UL94V-0	1	绿色	
4	压线框	黄铜	4	镀镍	
3	夹片	磷青铜	4	镀镍	
2	基座	PA66 UL94V-0	1	绿色	
1	螺钉	钢	4	镀锌	M2
序号	名称	材质	数量	电镀/颜色	备注

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING		TITLE插拔式接线端子PIN距3.5（4P）公插头REV.A			
CHECK					
APPROVAL					
TOLERANCES ARE		PART NO.LAIL-PTB3.5-4P-GN-01-MC	UNITS	mm	
30-150	±0.35				ANGLE
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
DWG.NO.		Projection 			