






Circuit Diagram

PCB Layout



NO.1	
PART NO	H
A	7.2
B	7.7



SPECIFICATION

- 1.Rating:DC 12V 50mA Max
- 2.Contact resistance:100mΩ MAX
- 3.Insulation resistance:100MΩ Min
- 4.Dielectric strength:250VAC/min
- 5.Operating force:250gf±80gf
- 6.Operating life:300,000 cycles
- 7.IP Rating:IP67

6	Stem	—	1	LCP	Black	—
5	Cover	—	1	SUS304	—	—
4	Plunger	—	1	RUBBER	Sky Blue	—
3	Contact Form	—	1	SUS301	Ag-PLATING	—
2	Housing	—	1	PA6T E430K	Black	—
1	Terminal	—	1	H65	Ag-PLATING	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS			DATE				
DRAWN	LIANG	2026.03.17					
CHECKED				TITLE:	TACT SWITCHES		
APPROVALS				PART NO.	K2-6262SP-□4SW-0		
TOLERANCES ARE	30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 	
	10~30	±0.20					
	5~10	±0.15					
	~ 5	±0.10					
			±2'	DRAWING NO.	_____		SHEET 1 OF 1

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.