







规格:


1. 额 定 值: DC30V 1.5A
2. 接触电阻: $\leq 50\text{m}\Omega$
3. 绝缘电阻: $\geq 100\text{M}\Omega$
4. 耐 电 压: 500VAC
5. 插 拔 力: 3N~30N
6. 使用寿命: 5000次
7. 使用温度: $-20^{\circ}\text{C} \sim +80^{\circ}\text{C}$



推荐插头尺寸



电路示意图



3	芯针	铜	镀铜锡	
2	弹片	铜	镀铜锡	
1	基座	PBT	黑色	
序号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	DC座
料 号 PART NO	HC-DC-015-2.5-03A

一般公差 TOLERANCE		比 例 SCALE	1:1			PART NO.	
X. ± 0.5	X. ° ± 5°	单 位 UNIT	MM	制 图 DRAW	AhYe		
.X ± 0.35	.X ° ± 2°	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云		
.XX ± 0.25	.XX ° ± 1°	版 本 REV	A	批 准 APPROVE	赵亮亮		
.XXX ± 0.15	.XXX ° ± 0.5°						

