




Model No.	POS.1	POS.2	POS.3
2AS1	ON	NONE	ON
Term. Comm.	2-3	N/A	2-1
SCHEMATIC			

SWITCH FUNCTION

邮箱：hooya89@hooya.hk
电话：0769-82310511-867

SPECIFICATIONS

MECHANICAL LIFE: 50,000 make-and-break cycles.
CONTACT RESISTANCE: 20 mΩ max. initial @ 2-4VDC
100mA for both silver and gold plated contacts.
INSULATION RESISTANCE: 1,000 MΩ min.
DIELECTRIC STRENGTH: 1,000 Vrms min. @sea level.
OPERATING TEMPERATURE: -40°C to 85°C.

MATERIALS

CASE & BUSHING - Glass filled nylon 6/6 , retardant ,
heat stabilized(UL94V-0)
ACTUATOR - Brass, chrome plated.Internal O-ring seal. standard
for all actuators.
TERMINALS/CONTACT - Copper alloy.
RoHS & Lead Free

	CONTACT PLATING	TERMINAL PLATING	RATINGS
Q	Silver	Q = Gold flash over silver	3 Amps @120 VAC or 28VDC
C	Gold over Silver	C = Gold over silver	1 Amps @250 VAC
R	Gold	R = Gold	0.4 Volt-Amps(VA) max. @20V max. (AC or DC)

东莞市弘皓电子有限公司

	符號	原尺寸	修改後尺寸	變更日期	SCALE (比例)： 3：2 TOLERANCE (公差)： 0.00 mm ± 0.25mm 0.0 mm ± 0.40mm ANGULAR：± 5° FILE NAME：2ASP0115	TITLE 圖 名		Sealed Sub - Miniature Toggle Switches		SIZE 圖紙	A4
1	Ⓐ		加註把手搖擺角度25°	MAY-28-2015		DWG NO. 圖 號	2AS1T1A1M2RES			UNIT 單位	inch mm
2	Ⓑ		操作溫度-30℃ 修訂為-40℃	JUL-26-2017		REV. 版 本	C	DATE 日 期	AUG - 11 - 2005	SHEET 張 數	1 of 1
3	Ⓒ					CHECKED BY 審 核				DRAWN BY 製 圖	BLUE
4	Ⓓ										
5	Ⓔ										