






2P-4P样式

5P-7P样式

8P-15P样式



SPECIFICATIONS

Applicable Wire: AWG.#30~#24

Voltage rating: 100V DC/AC

Current rating: 2A (AWG.#24)

Withstand voltage: 500V AC/min.

Working Temp: -25°C ~ +105°C

Insulation resistance: ≥500 MΩ

Contact resistance: ≤20 mΩ

MATERIAL

Housing: PA66, UL94-V0

备注:所有原料、零部件均符合最新ROHS2.0及REACH

PART NO	PIN	A	B
WAFER-GH1.5-2PJK	2	1.5	4.5
WAFER-GH1.5-3PJK	3	3.0	6.0
WAFER-GH1.5-4PJK	4	4.5	7.5
WAFER-GH1.5-5PJK	5	6.0	9.0
WAFER-GH1.5-6PJK	6	7.5	10.5
WAFER-GH1.5-7PJK	7	9.0	12.0
WAFER-GH1.5-8PJK	8	10.5	13.5
WAFER-GH1.5-9PJK	9	12.0	15.0
WAFER-GH1.5-10PJK	10	13.5	16.5
WAFER-GH1.5-11PJK	11	15.0	18.0
WAFER-GH1.5-12PJK	12	16.5	19.5
WAFER-GH1.5-13PJK	13	18.0	21.0
WAFER-GH1.5-14PJK	14	19.5	22.5
WAFER-GH1.5-15PJK	15	21.0	24.0

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: GH1.5 嵌壳	
		PAR	WAFER-GH1.5-NPJK
DECIMALS:	ANGLES:	DWN	Lucas
X.:±0.20	X.:±5°	CHKD	Ethan
X.X:±0.10	X.X':±3°	APVD	Jacob
X.XX:±0.05	X.XX':±1°	SCALE:1:1	UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1