


| 标 记<br>MARK | ECN编号/变更内容<br>ECN NO/DEFINITION | 修 改<br>REVISE | 日 期<br>DATE | 核 准<br>APPROVE |
|-------------|---------------------------------|---------------|-------------|----------------|
|             |                                 |               |             |                |
|             |                                 |               |             |                |

| H    |     |
|------|-----|
| 4.3  | 4.5 |
| 5.0  | 5.5 |
| 6.0  | 6.5 |
| 7.0  | 7.5 |
| 8.0  | 8.5 |
| 9.0  | 9.5 |
| 10.0 |     |










电 路 图

主要技术规格:

1. 额 定 值: 50mA DC12V
2. 接触电阻:  $\leq 50m\Omega$
3. 操 作 力:  $260 \pm 50gf$
4. 行 程:  $0.3 \pm 0.1mm$
5. 绝缘电阻:  $\geq 100M\Omega$
6. 抗电强度: 250V 50HZ 1Min.
7. 寿 命: 100,000 Cycles
8. 防水等级: IP67
9. 防银迁移: 60V, 85℃, 90%RH/60H

| 3   | 盖板  | PPA | 黑色    |     |
|-----|-----|-----|-------|-----|
| 2   | 簧片  | 不锈钢 | 覆银    |     |
| 1   | 基座  | PPA | 黑色    |     |
| 序 号 | 品 名 | 材 质 | 电镀/颜色 | 备 注 |

|                                                                                                   |                 |                |                 |                                                                                       |
|---------------------------------------------------------------------------------------------------|-----------------|----------------|-----------------|---------------------------------------------------------------------------------------|
|  深圳市虹成电子有限公司 |                 | 品 名<br>TITLE   | 轻触开关            |                                                                                       |
|                                                                                                   |                 | 料 号<br>PART NO | HC-QC6660-TFS-E |                                                                                       |
| GENERAL TOLERANCES<br>(UNLESS SPECIFIED)                                                          |                 | 比 列<br>SCALE   | 1:1             |  |
| >0.5~2                                                                                            | $\pm 0.10$      | 单 位<br>UNIT    | MM              | 制 图<br>DRAW                                                                           |
| >2~5                                                                                              | $\pm 0.25$      | 张 数<br>PART NO | 1 OF 1          | 审 核<br>CHECKED                                                                        |
| >5~10                                                                                             | $\pm 0.30$      | 版 本<br>REV     | A               | 批 准<br>APPROVE                                                                        |
| 角度                                                                                                | $\pm 0.5^\circ$ |                |                 |                                                                                       |



PCB. 焊接图