







Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS

Rated Current:3.0AMP
Contact Resistance:20mΩ Max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PBT
Max.Processing Temp: 180°C for 30-60 seconds
(200°C for 10 seconds)

Ordering Information

HC-JN 254 - * - N - * - * - * - **

No. of Rows
1=Single Row
2=Dual Row


No. of Pins
06-64Pin

Type
Z=直针
B=弯针
S=直插
R=弯插

Length
(Plastic)
(mm)

Material
默认=PBT
C=PA6T
E=PA9T
F=LCP

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

			GENERAL TOLERANCE	制 图 DRAWING	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD				
			DIM TOL	审 核 CHECK					
			X. X ±0.30	批 准 APPROVAL	产品名称 TITLE	筒牛2.54 双排 弯针	版 本 REV.	A	
1	初版发行		X. XX ±0.20	比 例 SCALE	产品料号 PART NO.	HC-JN254-2-N-W-8.8-XX	单 位 UNITS	mm	
		X. XXX ±0.10							
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	Angle ±3.0°	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1