



A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME



P.C.B LAYOUT

邮箱：hooya89@hooya.hk
电话：0769-82310511-867

- SPECIFICATION
- 1.Rating：20V DC/AC
Ubus 电流 5A Max, GND 电流1.25A Max,
Other PIN 0.25A Max
 - 2.Contact resistance: <50mΩ.
 - 3.Insulation resistance: >100MΩ (DC100V).
 - 4.Withstanding voltage: 100VAC .
 - 5.INSERTION FORCE: 5-20N/ REMOVAL FORCE: 8-20N
 - 6.life test: 10000 cycles.
 - 7.Operation temperature range:-25℃ ~ 85℃.
 - 8.Sign"* "is importance dimension.

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm > 1.5~5.0:±0.25mm > 5.0:±0.3mm	ANGULAR ±1°	A2	2023.12.12	更新图纸			TQF	GYW
							A1	2022.9.7	更新图纸			ZLK	GYW
							NO	DATE	REVISIONS			BY	APPD
4	HOOK	SUS	1		TITLE: TYPE C				UNIT : MM	ROHS	DWN		
3	SHELL	SUS	1	Ni-PLATED	MODEL: USB-310N-B-SU				SCALE: 1:1	COMPLIANT	CHK'D		
2	TERMINAL	BRASS	12	Au-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司						APPD		
1	HOUSING	LCP+30%GF	1	BLACK									
NO.	PART NAME	MATERIAL	QTY	FINISHING									
PRO.AGL:												REV :A2	