

A

B

C

D

E

F

G

A

B






C

D


E

F


G



推荐插头尺寸



电路示意图




P.C.B 设计参考尺寸

规格:

1. 额 定 值: DC30V 0.5A
2. 接触电阻: $\leq 30\text{m}\Omega$
3. 绝缘电阻: $\geq 100\text{M}\Omega$
4. 耐 电 压: 500VAC
5. 插 拔 力: 3N~30N
6. 使用寿命: 5000次
7. 使用温度: $-20^{\circ}\text{C} \sim +80^{\circ}\text{C}$

3	芯针	铜	镀铜锡	
2	弹片	铜	镀铜锡	
1	基座	PBT	黑色	
序号	品 名	材 质	电镀/颜色	备 注

 深圳市虹成电子有限公司		品 名 TITLE		DC座	
		料 号 PART NO		HC-DC-062-3. 0-03A	
一般公差 TOLERANCE		比 列 SCALE	1:1		
X. ± 0.5 .X ± 0.35 .XX ± 0.25 .XXX ± 0.15		单 位 UNIT	MM		
X. $^{\circ} \pm 5^{\circ}$.X $^{\circ} \pm 2^{\circ}$.XX $^{\circ} \pm 1^{\circ}$.XXX $^{\circ} \pm 0.5^{\circ}$		张 数 PART NO	1 OF 1	制 图 DRAW	AhYe
		版 本 REV	A	审 核 CHECKED	夏操云
				批 准 APPROVE	赵亮亮

