



HAOYU



SCHEMATIC



P.C.B LAYOUT

MATAL	X
SUS	0.2mm
PBS	0.25mm

PIN	$\phi 1.65$	$\phi 2.0$	$\phi 2.5$
APPD.		✓	

邮箱: hooya89@hooya.hk
电: 0769-82310511-867

					TOLERANCE UNLESS SPECIFIED							
					UP TO 5mm:±0.1	ANGULAR	A0	2020.11.30	首次发行		GYW	
					ABOVE 5mm:±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
5	DC005 PING	BRASS	1	Ni PLATED	TITLE:DC JACK				UNIT : MM	ROHS	DWN	
4	DC005 4#FLAT PIECE	BRASS	1	Ag PLATED	MODEL: DC-005-1-2.0-SU				SCALE: 4:1	COMPLIANT	CHK'D	
3	DC005 3#SPRING	SUS / PDS	1	Ag PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司						APPD	
2	DC005 COVER	PBT	1	BLACK/WHITE								
1	DC005 CASE	PBT	1	BLACK/WHITE								
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL: 		REV :A0	